

## MITOS VT6 CONTROL MODES

Several control modes can be selected. MITOS VT6 can be used to start/stop the motor, change its direction, modify its speed, or else, simply used as a remote display with no inverter control capability. Refer to following table for selecting MITOS VT6 control mode depending on inverter model:

Model	VF-NC3	VF-S15	VF-Mb1	VF-FS1	VF-AS1	VF-PS1
Control mode	Cmod =2	Cmod =2	Cmod =2	Cmod =2	Cmod =2	Cmod =2
	Fmod #3	Fmod #4	Fmod #4	Fmod #4	Fmod #5	Fmod #5
Frequency mode	Cmod #2	Cmod #2	Cmod #2	Cmod #2	Cmod #2	Cmod #2
	Fmod =3	Fmod =4	Fmod =4	Fmod =4	Fmod =5	Fmod =5
Control + Frequency mode	Cmod =2	Cmod =2	Cmod =2	Cmod =2	Cmod =2	Cmod =2
	Fmod =3	Fmod =4	Fmod =4	Fmod =4	Fmod =5	Fmod =5

## CONFIGURATION MENU



By pressing these keys together at start up, the VT6 configuration menu is entered.

### MENU CHOICES

Use arrow keys to move inside the Menu. Use the FWD and REV keys to make the selections and STOP/RESET key to exit the configuration menu. With this menu is possible to select and monitor:

- **Enabling of FWD and REV keys:** Use the FWD/REV key to enable or disable one or both keys.
- **Indication of Software release**
- **Unit Selection** of standard display suffix (select between Hz, RPM, m/min, none)
- **Select language** (English, Italian, Spanish, German, Russian)

- **Reset Frequency:** if ON and frequency control mode by VT6 is selected then the Set frequency is not automatically stored and every time inverter is OFF the frequency value is reset. If OFF, the last set frequency is always stored.
- **Transparent mode:** VT6 just used a s display

## MITOS VT6 MONITOR


Freq.= 0.0Hz  
Curr.= 0.0A

This is the **standard monitor display** for VT6.

If inverter is in RUN mode (motor running) the standard monitor display will show an animated arrow (↻) on the top right hand corner. The arrow will turn CW if the inverter receives a RUN FWD command and will turn CCW if the inverter receives a RUN REV command.

The scaling factor of the output frequency (Freq.) can be adjusted by changing parameter F710.

By pressing MON key the second line item can be changed between several variables:  
**output frequency, reference frequency, output current, input voltage, output voltage, last 4 alarms, total working time.**

In “**standard monitor display**”, if the VT6 is in frequency control mode and transparent mode is not active, the inverter output frequency can be changed directly  by pressing

The panel will enter frequency setting mode:

Set Frequency  
50Hz

Use the arrow keys to set the desired frequency.

MITOS VT6 is a **T.I.E.M.D.** product made in EU.

# MITOS

## VT6 rev.2.1

Advanced control panel  
for **Toshiba** Inverters



- **Multilanguage capability**
- **RS485 and TTY selectable interface**
- **Customizable front layout**
- **Suitable for inverter control and monitoring**

# SAFETY INFORMATIONS

## Mandatory



Please read this instruction manual before starting connection and operation of MITOS-VT6

## Warning



Please always give this manual to the end user of the MITOS-VT6 panel.

## Danger



Every time that a command is transferred from MITOS-VT6 panel to the Inverter, it is automatically stored into Inverter memory. If the connection cable between Mitos-b and Inverter is damaged, it will be impossible to keep the Inverter control (and stop the motor too). ALWAYS use safety devices to STOP the motor in emergency conditions

## General Cautions





MITOS-VT6 keypad can't be used in any device that could create danger to the human body or from which malfunction or incorrect operation would present direct threat to human life.

MITOS-VT6 keypad has been manufactured under strict quality controls. however, if it is used in critical equipment, where an error or a malfunction would cause serious accidents to persons or to the machine, safety devices MUST be installed on the equipment.


This manual could be subject to modifications without prior notice.

# OUTLINE DRAWING



External dimensions are exactly same of MITOS VT5, the previous model.

# PANEL CUT DIMENSIONS



Panel cut dimensions are indicative only.

# CONNECTION

MITOS VT6 can be connected to following TOSHIBA Inverters:


**VF-NC1, VF-NC3, VF-S9, VF-S11, VF-S15, VF-Mb1, VF-FS1, VF-A7, VF-P7, VF-AS1 and VF-PS1.**

**Connection is made through standard 8 pin RJ45 pin to pin cables.**

For inverters with TTL port the maximum cable length is limited to 15 meters. For inverters with RS485 port the length of the cable can be greater.

Connection type can be selected by switches on the back of the MITOS VT6 as shown below:

## RS485



VF-NC3  
VF-S15  
VF-Mb1  
VF-FS1  
VF-PS1  
VF-AS1

## TTL



VF-NC1  
VF-S9  
VF-S11  
VF-P7  
VF-A7

# FUNCTIONS OF KEYS



Run motor in forward direction if VT6 control is selected.	Run motor in reverse direction if VT6 control is selected.	Change inverter frequency if VT6 control is selected and scroll items in monitor mode	Enter function	Stop motor if VT6 control is selected. Reset inverters alarms in all mode
--	--	---	----------------	---